

# Xerox® DocuMate™ 4830i

## Versatile scanning solution for large documents

- Perfect for a wide variety of documents, up to A3 size
- 50 ppm in simplex and 100 ipm in duplex\*
- Ultrasonic double feed detection
- One Touch scanning to any of 9 destinations at the touch of a button
- Create searchable PDF files making scanned documents easy to find
- Automatic image enhancement tools without the need of user intervention

\* Landscape at 300 dpi b/w & grayscale

### High Volume and Performance Solution

The Xerox® DocuMate™ 4830i scanner is an effective way to manage large-sized documents and import them to a content management solution in a single step.

It has a friendly interface that allows the user to simply insert their document, and then press the Simplex or Duplex button on the front panel to initiate scanning and automatically email, print, convert or share their file.. The buttons are present at the optimal resolution, colour depth, file format and paper size for common scanning tasks, but of course can be easily changed at any time.

### Secure and Reliable

Regulatory compliance requirements have dramatically increased the need for companies to implement reliable records management. Document capture solutions have also been essential to meet the everyday document imaging needs of paper intensive offices.

The DocuMate™ 4830i includes software tools to edit, crop and retouch scanned images and organise the files into folders. With the touch of a button, users are able to scan and automatically store, optical character recognition (OCR), print, attach or view their documents in a range of locations from their desktop to their storage cloud.

Businesses ranging from (not limited to) healthcare, transportation and industrial manufacturing markets that handle and manage substantial quantities of paper will immediately appreciate the functionality and reliability of the DocuMate™ 4830i.

#### Smart OCR

transform scanned documents into editable text

#### Two-way Design

that accommodates a wide variety of documents.

#### Automatic image enhancement tools

without the need of user intervention



**ADF** – For efficient scanning of forms, invoices, or standard documents



**Flatbed** – For convenient scanning of fragile documents and accommodates even thick books up to A3 size



# Xerox® DocuMate™ 4830i Software Solutions

## Visioneer®

### OneTouch

OneTouch provides the most efficient ease-of-use scanning experience to improve your work flow. OneTouch enables the Xerox® DocuMate™ 4830i scanner to send your scanned documents to nearly any destination of your choice all at the touch of a button. The files can be automatically delivered to a specific folder, email, Microsoft Office Application, a local or network printer, a custom application or your cloud storage.

### Acuity

With the use of advanced algorithms and dynamic thresholding, Acuity aims to improve the visual clarity of every document that you

scan. This technology enables your scanner to instantly correct documents containing imperfections, it improves the overall quality of scanned images, increases increases OCR accuracy and most importantly saves your time.

### DriverPLUS

DriverPLUS is a new generation of innovative driver technology for Xerox® DocuMate™ scanners that enables a superior experience for both users and system integrators.

### Nuance®

### OmniPage® Pro

OmniPage Pro provides a precise OCR and layout retention solution that quickly

transforms scanned documents into editable and formatted text. The text can then be used in virtually any word processing, desktop or web publishing program.



### PDF Converter

Nuance PDF Converter is the smarter PDF software choice for businesses. It combines superior Microsoft Office Support, powerful functionality, built-in intelligence, DMS integration and intuitive ease of use. Nuance PDF converter provides everything you need in order to create, convert, edit, assemble and securely share PDF files.

### Office Gemini®

### Dokmee Capture

Dokmee Capture high production scanning software provides all the features required for document capture, processing and reporting. It allows businesses both large and small to easily convert their scanned documents into digital files, capture images and data contained in them, and then transform it into organised searchable information. This mission-critical business information is then placed into a centralised location to be easily searched, stored and retrieved when needed.

### Image Enhancement



Original



Raw Scan



Acuity Enhanced Scan

### Xerox® DocuMate™ 4830i Product Specifications

Type	Desktop ADF with Flatbed	
Scan Speed	Black & White @ 200 & 300 dpi	50 ppm / 100 ipm duplex
	Colour @ 200 & 300 dpi	30 ppm / 60 ipm duplex
Optical Resolution	600 dpi	
Output Bit Depth	24-bit colour, 8-bit grayscale, 1-bit black & white	
Imaging Sensor	CIS (Contact Image Sensor)	
Light Source	LED (Light Emitting Diode)	
Scan Method	Fast duplex ADF and Simplex Single-pass Flatbed	
Interface	Hi-Speed USB 2.0 (1.1 compatible)	
Driver	TWAIN, WIA, ISIS, Visioneer Driver Plus	
Detection	Ultrasonic Double Feed Detection	
ADF Minimum Document Size	102 x 105 mm	
ADF Maximum Document Size	297 x 2997 mm	
Maximum Flatbed Scanning Area	297 x 420 mm	
ADF Capacity	75 sheets	
Duty Cycle	3,000 pages/day	
Dimensions (W x D x H)	581 x 499 x 194 mm	
Weight	12 kg	
Background Colour	ADF: Gray	Flatbed: Black

### Options and Consumables

Type	Product Code	Description
Consumables	800L08333	Pad Assembly (30,000 pages)
	800L08334	Roller Assembly (200,000 pages)
Accessories	800L08336	Net Scan

For more information or detailed product specifications, please contact us at:

**Fuji Xerox Asia Pacific Pte.Ltd.** (993478-A)  
(Fuji Xerox Printers)  
1st Floor, No. 10, Jalan Bersatu 13/4,  
46200 Petaling Jaya, Selangor, Malaysia.  
Tel: 03-2191 1888 Fax: 03-7882 2767

**East Malaysia Office:**  
199A-201, Lot 3049 & 3050, Eastmoore Centre,  
2½ Mile, Jalan Rock, 93200 Kuching,  
Sarawak, Malaysia.  
Tel: 082-428 650 Fax: 082-418 733

Service Hotline : 1800 88 1063  
www.fujixeroxprinters.com.my

### Minimum System Requirements

- Intel® Pentium® 4
- Windows 8 / 7 / Vista® / XP®
- 2GB RAM
- 350 MB available hard drive space
- DVD-ROM drive
- USB 2.0 port

### Bundle Software

- Visioneer OneTouch
- Visioneer Acuity
- Nuance OmniPage Pro
- Nuance PDF Converter Pro
- Office Gemini Dokmee Capture\*\*

\*\*Dokmee Capture is not supported on Microsoft Windows XP

### In Box Item

- Power Supply
- USB Cable
- Quick Install Guide
- Technical Support Card
- DVD-ROM (PC Software)

